

CROSSFIRE Ultra-Low Power Chemical Injection Pump

Introduction

The LCO Technologies *CROSSFIRE* Chemical Injection pump is an ultra-low power device that is designed to reduce chemical costs, maintenance costs and methane emissions. It is a durable, energy-efficient solution like no other that can run for weeks – not days, even in areas with limited sunlight. It can be configured with one to four fluid ends, allowing you to replace up to four pneumatic pumps with one unit.

Features

The *CROSSFIRE* chemical injection pump includes the following key features and benefits:


- Eliminates methane venting from chemical injection
- Precise chemical injection
 - Delivers chemical proportionate to flow
 - Consistent chemical dispersion rate
 - Delivers <1L/day to 720 L/day up to 10,000 psi
- High system autonomy
 - o Ultra-low power chemical injection pump that can run weeks, not days on most applications
- Standard 5100 series fluid ends for field familiarity
 - Customization available for fluid end size, packings, and O-rings based on application
- Comes complete with a smart controller that has MODBUS communications built in as a standard
 Option to upgrade to an advanced controller that has standalone automation capabilities
- User friendly operator and technician interface that is password protected

Explosion Proof Motor Assembly

- Class 1, Division 1 Group CD T6 Explosion Proof Motor Assembly
- Rated input 24 Vdc, 9.9 Amps, 750 rpm, Class B, Continuous Stall Current 11A, Rated output power 190W
- Ambient Temperature: -40 C to +60 C
- Efficient, compact and powerful permanent rare earth magnet motor

Planetary Gearbox

- Custom design with double support mechanism for increased durability and stability
- Double stage, 20:1 ratio to deliver high torque to the pump assembly
- Closed casing to keep dust and contaminant free
- Lifetime lubrication, no maintenance required



Smart Controller Features

- Sophisticated Field Oriented Control (FOC) scheme used to drive the 3-phase rare earth permanent magnet BLDC motor for maximum torque performance and efficiency
- Sensorless design with no Hall Effect sensor signal required for control
- Only 3 (plus ground) standard conductor flex armour cables required to power the motor
 - Cable length: maximum 60ft long (gauge 10)
 - Longer cables are acceptable with larger gauge conductors
- Built in protection schemes to protect equipment such as: ground-fault, over-voltage, over-current, undervoltage, short-circuit, reverse polarity from power supply, unbalanced loading due to broken / loose motor power lines, and fast logic to shut down and isolate motor in the event of faults
- Direction of motor rotation is reversed automatically every month to increase life span of the cam box and minimize natural wear and tear
- Permanent record of total stroke counts, volume of chemical injected for each plunger, system status and operating conditions. Data can be accessed remotely via SCADA or with the use of the local operator interface and is time and date stamped.

Process Control and Programmable Logic:

- Specific programmable logic and control algorithm can be developed to meet customer needs
- Built-in process control functions, such as toggle switch control, plunger lift control, timer control, PID, ratio and feedback controls
- Multiple digital and analog IO's to transmitters and final control elements
- Serial communication to a data modem, RTU or flow computer, pole top Bluetooth module, or HMI
- Supports standard MODBUS/RTU protocol for remote control and monitoring

Software Interface

LCO Technologies' *CROSSFIRE* Software Interface is a tool that allows for easy configuration and monitoring of the controller for the *CROSSFIRE* platform. By connecting to the controller's RS232 serial port from a Windows computer, both operators in the field and technicians performing more advanced setup of the controller can monitor and configure the device from a simple, intuitive interface.

The software's password protected separation of roles between operator and technician, allows the user to be presented only with the information and options required for their task. This eliminates distraction and reduces the chance of accidental misconfiguration.

A mobile version of the software is also available, allowing users of iOS smartphones and tablets to connect to and configure the controller, using the RS232 Bluetooth LE adapter available for the controller.

Specs/software requirements:

- A computer with either Windows XP/7/8.1/10 or later
- 512 MB RAM
- 50 MB hard drive space

Hazardous Area Certifications

The CROSSFIRE has the following hazardous certifications:

- The Explosion Proof Motor Assembly (Model LCOM-1000)
 - CSA certified to Class 1 Division 1 Groups CD T6 Rated input 24 VDC, 9.9 Amps, 750 rpm maximum, Class B, Continuous Stall Current 11 A, Rated Output Power 190W Ambient Temperature -40°C to +60°C
- The Smart Controller (Model LCOC-1000-A and Model LCOC-1000-B)
 - CSA certified to Class 1, Division 2, Groups CD T4
 - Rated Input 24 VDC, Vac, 9.9 Amps Rated Output 24 VDC, 9.9 Amps
 - Ambient Temperature: -40°C to +60°C

Integration with Chemical Manager

The versatility of the *CROSSFIRE* controller facilitates use between the controller and several Emerson RTU based smart applications such as Chemical Manager & Local Display Manager. Modbus communications between the RTU and the controller have been pre-mapped and this out of the box solution requires very little configuration. Several advantages of coupling the *CROSSFIRE* & Chemical Manager have been listed below:

- Improved operation visibility of current chemical status and demand outlook
- Detailed tank inventory data (Fill info, chemical expiration, live values, and alarming)
- Built in and user defined inhibits

Mounting Bracket

The *CROSSFIRE* mounting bracket is light weight, low-cost and simple. When clamped on to the *CROSSFIRE*, it brings the unit 1.5" out of the drip tray and has the same bolt pattern as the Texsteam 5100 pneumatic pumps for easy field integration.



Vee Packing Temperature Rating

Material	Minimum Temperature	Maximum Temperature
Buna N	-40 °C	+120 °C
Viton	-26 °C	+204 °C
Teflon	-268 °C	+232 °C
Flurosilicone	-56 °C	+204 °C
Rockhard	-40 °C	+120 °C


Maximum Operating Conditions

Fluid End Maximum Pressure Rating (psi)					Injection Range*			
Size	Zebra Buna/PTFE	Buna	Teflon	Viton	Flurosilicone	RockHard	(L/day)	
1/2"	2500	2500	3000	2500	3000	3000	4.6 L/day - 171.4 L/day	
3/8"	4000	3000	3000	3000	3000	6000	2.6 L/day - 96.4 L/day	
1/4"	6000	3000	3000	3000	3000	6000	1.2 L/day - 42.9 L/day	
3/16"	6000	3000	3000	3000	3000	6000	0.7 L/day - 24.1 L/day	

*Note: The pumping volumetric efficiency of the fluid end will decrease with an increase in discharge pressure. Values listed are theoretical and based on one fluid end.

LCOC-PUMP Specifications

CPU Module				
Processor	NXP 1769 micro	NXP 1769 microcontroller with ARM Cortex M3 processor		
Memory	SRAM – 64 KB			
	Flash: 512 KB			
	Onboard flash: 6	64MB (Advanced Model only)		
Clock	Crystal oscillator	Crystal oscillator: 120 MHz		
	Battery backed F	Real-Time clock		
	Watchdog timer			
Communicatio	ons			
Ports	COM 1	3-wire RS232 for data modem or Bluetooth pole-top module		
		Maximum cable length: 130 ft.		
	COM 2	RS232 DB9 connector		
		Supports operator interface via a serial cable or with a Bluetooth dongle		
		Maximum cable length: 25 ft.		
		Maximum Bluetooth range: 50 ft.		
	Modbus COM	2 or 3-wire RS485 for RTU, SCADA and HMI		
		Maximum cable length: 4000 ft.		
		Ethernet 10/100 - Maximum cable length: 350 ft (Advanced model only)		
Protocols	Serial Modbus/R	TU slave support on the RS485 port		
	Serial communic	ation in ASCII on COM1 and COM2		
LED				
	Advanced	16 LED's to indicate system status, digital IO's and COM port traffic		
	Basic	12 LED's to indicate system status, digital IO's and COM port traffic		





	1 reset button to r	eboot controller. Press with a pin	
IO Specs			
Controller	Advanced	4 Digital Inputs, 4 Digital Outputs, 3 Analog Inputs and 1 Analog Output	
	Basic	2 Digital Inputs, 2 Digital Outputs, 3 Analog Inputs	
		DI1-DI3 are discrete	
		DI4 is pulse count input (Advanced model only)	
		All Digital Outputs are discrete	
Digital Inputs	Input Type	DI1-DI3: Discrete level	
		DI4: Pulse count input	
	Isolation	Each channel is individually isolated	
	Voltage	10-36 Vdc	
	Scan Rate	100 ms for discrete level. 400 us interrupt for pulses	
	Frequency	Maximum 10 KHz pulse input	
	Loop Power	Externally sourced	
	Input Resistance	20,000 Ohm	
Digital Outputs	Output Type	Dry contact	
	Isolation	Each channel ground is individually isolated	
	Voltage	10 – 36 Vdc	
	Scan Rate	100 ms for discrete level	
	Loop Power	Externally sourced	
	Output Current	Maximum 1.0 A at 24 Vdc	
Analog Inputs	Input Type	4-20 mA on 250 Ohm resistor or 0 - 5 V direct, software selectable	
	Isolation	All analog channels share the same ground	
	Scan Rate	100 ms	
	Loop Power	Externally sourced	
Analog Outputs	Output Type	0 – 5 V	
	Isolation	All channels share the same ground isolated	
	Scan Rate	100 ms	
	Loop Power	Internally sourced	
Power			
	External DC Powe	er Supply: 24 Vdc, however will function within 18 – 30 Vdc range	
	Controller Power	consumption: 35 mA @ 24 Vdc	
	Real-Time Clock	pattery: 3V Lithium button type CR2032	
Physical			
Controller	Construction	Fibre glass base plate and top cover	
	Mounting	Bolt down to panel backplane with 4 screws or mount with 2 DIN-rail clips	
	Dimensions	145 mm W by 240 mm L by 27.6 mm	
	Weight	470 g	

© 2017, LCO Technologies LTD. All rights reserved. (V4.1)

	FIRE Chemic	cal Injection Pump	Product Data Shee	
	Wiring	24 Vdc power supply: 10 AWG, Max 60 ft		
		Motor power lines: 10 AWG, Max 60 ft		
		Digital and Analog I/O: size 20 to 24 AWG		
	Wiring Access	Easy access from the top		
Environmental				
	Operating Temperature: -40 C to +60 C			
	Storage Temperature: -50 C to +85 C			
	Operating Humidity: 5 to 95%, non-condensing			
Regulatory Appro	vals for Hazardous	s Locations		
CSA Certification				
	Controller	Class 1, Division 2, Groups CD T4		
	Motor Assembly	Class 1, Division 1, Groups CD T6		

Dimensional Drawing:





Overall Dimensions: H: 16.51 in W: 21.83 in L: 21.83 in